



 newskill

# SEIRYU

S P E C T R U M  
MEMBRANE KEYBOARD



## SPECIAL FEATURES

- Macro backlit corded keyboard.
- 18 group of macro recording function keys.
- 26 keys anti-ghosting.
- 3 kinds of color backlighting.
- Six commonly used multimedia key design.
- 4 Blue status ;LEDs.
- Macro recording key is lower than other key cap design.

## INSTALLATION

1. Connect the device to an available USB port of your PC.
2. Installation of the device is automatical after its connection to a PC USB port.
3. If the device not working, please disconnect the keyboard from your PC and check connect pins for possible damage.

## RECORD MACRO INSTRUCTIONS

- Recording function of G1 key in Model 1 (M1)
  1. Press button "M1" and "MR", and the 4 LED indicator flashes slowly and evenly.
  2. Press button "G1", the LED indicator rapid flashes.
  3. You can start the macro recording now and press the keys that you want.

Note: The recording capacity is 30 bytes maximal, and limited recording time is 30s maximal, if you exceed capacity or time, recording automatically exit.

  4. Press "MR" for save recording, the LED indicator back to normal state. You can redo the steps above if you recording failure.
- About program G2~G6 in Model 1 (M1) same as above, just need change "G1" to G2/G3/G4/G5/G6 in second step as above.
- About program G1~G6 have more function, you have to make recording in different Models, just change the button "M1" to M2/M3 in first step.

## 26 KEYS ANTI-GHOSTING



Q, A, Z, W, S, X, E, D, C, R, F, V, T, G, B, M, Arrow keys, Tab, Caps lock, Shift-L, Ctrl-L, Alt-L, Space key

PLAY/PAUSE

RECORDING

MODE

BACKLIT  
SWITCH

MUTE

PREVIOUS

STOP

NEXT

MACRO

WINDOWS

F<sub>n</sub> KEY



TECHNICAL SPECIFICATION

Keyboard type	Macro Backlit Keyboard
Communication technology	wired
OS compatibility	Windows XP/Vista/7/8/10
Cyrillic alphabet layout	Windows
Number of keys	104 pcs
Number of shortcut keys	6 pcs
Number of Macro keys	10 pcs
Interface	USB
Keys contact	membrane with tactile feedback
Error-free running time	more than 20,000,000 strokes
Dimensions	492 × 40 × 203 (mm)
Weight	1126 (g)
Life time	2 years





 **SEIRYU** S P E C T R U M  
MEMBRANE KEYBOARD